


# Q4140-1 Cut Sheet



Quabbin control and signal cable, unshielded, 2 conductors, 18 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q4140-1>

## Technical Specifications

|                                      |                    |
|--------------------------------------|--------------------|
| <b>Brand</b>                         | Quabbin            |
| <b>Item</b>                          | Cable              |
| <b>Wire/Cable Type</b>               | Control and signal |
| <b>UL Wire/Cable Type</b>            | CM and AWM         |
| <b>Applicable Standards</b>          | UL 2095            |
| <b>Application</b>                   | General purpose    |
| <b>Flexibility</b>                   | Semi-flexible      |
| <b>Voltage Rating</b>                | 300V               |
| <b>Conductors</b>                    | 2 conductors       |
| <b>Conductor Size</b>                | 18 AWG             |
| <b>Conductor Stranding</b>           | 7-stranded         |
| <b>Conductor Material</b>            | Tinned copper      |
| <b>Conductor Insulation Material</b> | PVC                |

|                                       |  |
|---------------------------------------|--|
| <b>Conductor Insulation Color</b>     | Color Code 1   |
| <b>Shielding</b>                      | Unshielded   |
| <b>Jacket Material</b>                | PVC  |
| <b>Jacket Color</b>                   | Gray   |
| <b>Nominal Overall Cable Diameter</b> | 0.21in   |
| <b>Bulk Length</b>                    | Cut to length  |
| <b>Package Type</b>                   | 1 to 99ft = Coil, 100 to 885ft = 14 x 7in Reel, 886 to 1265ft = 14 x 10in Reel, 1266 to 1935ft = 16 x 10in Reel, 1936 to 2705ft = 18 x 10in Reel, 2706 to 3520ft = 18 x 13in Reel, 3521 to 7875ft = 24 x 17in Wooden Reel, 7876 to MAX = 30 x 17in Wooden Reel |

## Agency Approvals

|                         |   |
|-------------------------|---|
| <b>UL Listed File #</b> | E118830, E69976   |
| <b>CSA File #</b>       | LL51726   |
| <b>RoHS Status</b>      | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>         | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>            | <a href="#">RoHS Statement</a>                                      |