


Q5082-1 Cut Sheet



Quabbin Datamax continuous flexing Cat5e industrial Ethernet cable, shielded, 2 twisted pairs, 26 AWG, 7-stranded, tinned copper, HDPE conductor insulation material, Zero Halogen Flame Retardant (ZHFR) jacket, teal, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q5082-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Series	Datamax
Protocol	Ethernet
Wire/Cable Type	Cat5e industrial Ethernet
UL Wire/Cable Type	CMX
Application	Data
Flexibility	Continuous flexing
Voltage Rating	300V
Conductors	2 twisted pairs
Conductor Size	26 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	High-density polyethylene (HDPE)

Conductor Insulation Color	Pair 1: orange, white/orange and Pair 2: green, white/green
Shielding	Shielded
Jacket Material	Zero Halogen Flame Retardant (ZHFR)
Jacket Color	Teal
Nominal Overall Cable Diameter	0.233in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 722ft = 14 x 7in Reel, 723 to 1031ft = 14 x 10in Reel, 1032 to 1596ft = 16 x 10in Reel, 1597 to 2247ft = 18 x 10in Reel, 2248 to 2922ft = 18 x 13in Reel, 2923 to 6276ft = 24 x 17in Wooden Reel, 6277 to 10318ft = 30 x 17in Wooden Reel, 10319 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	ETL 3185754
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement