

SOH-25C-9.525 Cut Sheet



Sung-II Machinery drive coupling hub, Oldham, aluminum alloy, clamp, size 25, 3/8in bore. Requires SOH-25-DISC torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOH-25C-9.525>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Oldham
Material	Aluminum alloy
Rated Torque	2.5 N·m
Maximum Torque	5 N·m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	2mm
Maximum RPM	10000

Attachment Style	Clamp
Coupling Size	25
Overall Length	32mm
Bore Diameter	3/8in
Outside Diameter	25.5mm
Clamp Screw Fastening Torque	1.7 N·m
Clamp Screw Size	M3-0.5 x 10mm
Requires	SOH-25-DISC torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SOH-25C-9.525.pdf>
See store item page for other formats.