

SOH-32C-10 Cut Sheet



Sung-II Machinery drive coupling hub, Oldham, aluminum alloy, clamp, size 32, 10mm bore. Requires SOH-32-DISC torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOH-32C-10>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Oldham
Material	Aluminum alloy
Rated Torque	7 N-m
Maximum Torque	14 N-m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	2.5mm

Maximum RPM	9000
Attachment Style	Clamp
Coupling Size	32
Bore Diameter	10mm
Outside Diameter	32mm
Clamp Screw Fastening Torque	3.5 N-m
Clamp Screw Size	M4
Requires	SOH-32-DISC torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SOH-32C-10.pdf>
See store item page for other formats.