


Q5506-1 Cut Sheet



Quabbin Datamax Cat5e Ethernet cable, unshielded, 4 twisted pairs, 26 AWG, 7-stranded, tinned copper, polyethylene conductor insulation material, PVC jacket, blue, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q5506-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Series	Datamax
Protocol	Ethernet
Wire/Cable Type	Cat5e Ethernet
UL Wire/Cable Type	CMR and CMG
Applicable Standards	UL 444 and UL 1666
Application	Data
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	4 twisted pairs
Conductor Size	26 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	Polyethylene

Conductor Insulation Color	Pair 1: blue, white/blue, Pair 2: orange, white/orange, Pair 3: green, white/green and Pair 4: brown, white/brown
Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Blue
Nominal Overall Cable Diameter	0.215in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 845ft = 14 x 7in Reel• 846 to 1205ft = 14 x 10in Reel• 1206 to 1850ft = 16 x 10in Reel• 1851 to 2580ft = 18 x 10in Reel• 2581 to 3355ft = 18 x 13in Reel• 3356 to 5000ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement