

SOH-32C-13 Cut Sheet



Sung-II Machinery drive coupling hub, Oldham, aluminum alloy, clamp, size 32, 13mm bore. Requires SOH-32-DISC torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOH-32C-13>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Oldham
Material	Aluminum alloy
Rated Torque	7 N·m
Maximum Torque	14 N·m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	1.5mm
Maximum RPM	9000

Attachment Style	Clamp
Coupling Size	32
Overall Length	44.7mm
Bore Diameter	13mm
Outside Diameter	32mm
Clamp Screw Fastening Torque	3.5 N·m
Clamp Screw Size	M4-0.7 x 12mm
Requires	SOH-32-DISC torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SOH-32C-13.pdf>
See store item page for other formats.