


Q5752-1 Cut Sheet



Quabbin continuous flexing Cat5e industrial Ethernet cable, unshielded, 4 twisted pairs, 24 AWG, 7/32-stranded, tinned copper, HDPE conductor insulation material, FR-TPE jacket, teal, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q5752-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Protocol	Ethernet
Wire/Cable Type	Cat5e industrial Ethernet
UL Wire/Cable Type	CMX and AWM
Applicable Standards	UL 2463
Application	Data
Flexibility	Continuous flexing
Voltage Rating	600V
Conductors	4 twisted pairs
Conductor Size	24 AWG
Conductor Stranding	7/32-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	High-density polyethylene (HDPE)
Conductor Insulation Color	Pair 1: blue, white/blue, Pair 2: orange, white/orange, Pair 3: green, white/green and Pair 4: brown, white/brown

Shielding	Unshielded
Jacket Material	FR-TPE
Jacket Color	Teal
Nominal Overall Cable Diameter	0.248in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 630ft = 14 x 7in Reel, 631 to 910ft = 14 x 10in Reel, 911 to 1400ft = 16 x 10in Reel, 1401 to 1980ft = 18 x 10in Reel, 1981 to 2570ft = 18 x 13in Reel, 2571 to 5530ft = 24 x 17in Wooden Reel, 5531 to 9100ft = 30 x 17in Wooden Reel, 9101 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement