

SOH-57C-19 Cut Sheet



Sung-II Machinery drive coupling hub, Oldham, aluminum alloy, clamp, size 57, 19mm bore. Requires SOH-57-DISC torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOH-57C-19>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Oldham
Material	Aluminum alloy
Rated Torque	34 N-m
Maximum Torque	68 N-m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	3.5mm

Maximum RPM	6000
Attachment Style	Clamp
Coupling Size	57
Bore Diameter	19mm
Outside Diameter	57mm
Clamp Screw Fastening Torque	13 N-m
Clamp Screw Size	M6
Requires	SOH-57-DISC torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SOH-57C-19.pdf>
See store item page for other formats.