

SRB-19C-4.93-5 Cut Sheet



Sung-II Machinery drive coupling, servo-beam, 7075-T6 aluminum alloy, clamp, size 19, 4.93 x 5mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRB-19C-4.93-5>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo-beam
Material	7075-T6 aluminum alloy
Rated Torque	0.6 N·m
Maximum Torque	1.2 N·m
Maximum Angular Misalignment	2.5 degrees
Maximum Parallel Misalignment	0.15mm
Maximum RPM	20000

Attachment Style	Clamp
Coupling Size	19
Overall Length	23mm
Bore Diameter	4.93mm
Bore Diameter 2	5mm
Outside Diameter	19.1mm
Clamp Screw Fastening Torque	1 N·m
Clamp Screw Size	M2.6-0.45 x 8mm

Agency Approvals

UL Listed File #	NONE
UL Recognized File #	NONE
UL Hazardous File #	NONE
CSA File #	NONE
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SRB-19C-4.93-5.pdf>
See store item page for other formats.