


Q6100-1 Cut Sheet



Quabbin control and signal cable, unshielded, 4 conductors, 20 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q6100-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	4 conductors
Conductor Size	20 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black, white, red and green

Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.219in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 817ft = 14 x 7in Reel, 818 to 1167ft = 14 x 10in Reel, 1168 to 1806ft = 16 x 10in Reel, 1807 to 2544ft = 18 x 10in Reel, 2545 to 3307ft = 18 x 13in Reel, 3308 to 7104ft = 24 x 17in Wooden Reel, 7105 to 11680ft = 30 x 17in Wooden Reel, 11681 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E69976,E118830
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement