


Q6130-1 Cut Sheet



Quabbin control and signal cable, unshielded, 1 twisted pair, 20 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q6130-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	1 twisted pair
Conductor Size	20 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black and red

Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.192in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 973ft = 14 x 7in Reel, 974 to 1063ft = 14 x 10in Reel, 1064 to 1519ft = 16 x 10in Reel, 1520 to 2351ft = 18 x 10in Reel, 2352 to 3310ft = 18 x 13in Reel, 3311 to 4303ft = 24 x 17in Wooden Reel, 4304 to 9243ft = 30 x 17in Wooden Reel, 9244 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement