


# Q6151-1 Cut Sheet



Quabbin control and signal cable, shielded, 2 twisted pairs, 20 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q6151-1>

## Technical Specifications

<b>Brand</b>	Quabbin	<b>Conductor Insulation Color</b>	Pair 1: black, red and Pair 2: green, white
<b>Item</b>	Cable	<b>Shielding</b>	Shielded
<b>Wire/Cable Type</b>	Control and signal	<b>Jacket Material</b>	PVC
<b>UL Wire/Cable Type</b>	CM and AWM	<b>Jacket Color</b>	Gray
<b>Applicable Standards</b>	UL 2464	<b>Nominal Overall Cable Diameter</b>	0.225in
<b>Application</b>	General purpose	<b>Bulk Length</b>	Cut to length
<b>Flexibility</b>	Semi-flexible	<b>Package Type</b>	1 to 99ft = Coil, 100 to 770ft = 14 x 7in Reel, 771 to 1100ft = 14 x 10in Reel, 1101 to 1685ft = 16 x 10in Reel, 1686 to 2360ft = 18 x 10in Reel, 2361 to 3065ft = 18 x 13in Reel, 3066 to 6860ft = 24 x 17in Wooden Reel, 6861 to MAX = 30 x 17in Wooden Reel
<b>Voltage Rating</b>	300V		
<b>Conductors</b>	2 twisted pairs		
<b>Conductor Size</b>	20 AWG		
<b>Conductor Stranding</b>	7-stranded		
<b>Conductor Material</b>	Tinned copper		
<b>Conductor Insulation Material</b>	PVC		

## Agency Approvals

<b>UL Listed File #</b>	E118830, E69976
<b>CSA File #</b>	LL51726
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>