

Q7115-1 Cut Sheet



Quabbin control and signal cable, unshielded, 2 conductors, 22 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q7115-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	2 conductors
Conductor Size	22 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black and red

Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.164in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 1457ft = 14 x 7in Reel, 1458 to 2082ft = 14 x 10in Reel, 2083 to 3221ft = 16 x 10in Reel, 3222 to 4536ft = 18 x 10in Reel, 4537 to 5898ft = 18 x 13in Reel, 5899 to 12668ft = 24 x 17in Wooden Reel, 12669 to 20828ft = 30 x 17in Wooden Reel, 20829 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E69976,E118830
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement