


Q7135-1 Cut Sheet



Quabbin control and signal cable, unshielded, 6 conductors, 22 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q7135-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	6 conductors
Conductor Size	22 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black, white, red, green, orange and blue

Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.209in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 821ft = 14 x 7in Reel, 822 to 897ft = 14 x 10in Reel, 898 to 1282ft = 16 x 10in Reel, 1283 to 1984ft = 18 x 10in Reel, 1985 to 2794ft = 18 x 13in Reel, 2795 to 3632ft = 24 x 17in Wooden Reel, 3633 to 7800ft = 30 x 17in Wooden Reel, 7801 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement