


Q8180-1 Cut Sheet



Quabbin control and signal cable, shielded, 6 conductors, 24 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q8180-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	6 conductors
Conductor Size	24 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black, white, red, green, brown and blue

Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.2in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 897ft = 14 x 7in Reel, 898 to 980ft = 14 x 10in Reel, 981 to 1400ft = 16 x 10in Reel, 1401 to 2166ft = 18 x 10in Reel, 2167 to 3051ft = 18 x 13in Reel, 3052 to 3966ft = 24 x 17in Wooden Reel, 3967 to 8518ft = 30 x 17in Wooden Reel, 8519 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement