SRBA-39C-10-12 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Sung-Il Machinery drive coupling, servo-beam, 7075-T6 aluminum alloy, clamp, size 39, 10 x 12mm bore.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/SRBA-39C-10-12

Technical Specifications

Brand	Sung-Il Machinery
Item	Drive coupling
Coupling Type	Servo-beam
Material	7075-T6 aluminum alloy
Rated Torque	7 N·m
Maximum Torque	14 N·m
Slip Torque	12 N·m
Maximum Angular Misalignment	2.5 degrees
Maximum Parallel Misalignment	0.25mm

Maximum RPM	10000
Attachment Style	Clamp
Coupling Size	39
Overall Length	43mm
Bore Diameter	10mm
Bore Diameter 2	12mm
Outside Diameter	39mm
Clamp Screw Fastening Torque	8 N·m
Clamp Screw Size	M5-0.8 x 16mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/SRBA-39C-10-12.pdf
See store item page for other formats.