

# SRBA-39C-12-14 Cut Sheet



Sung-II Machinery drive coupling, servo-beam, 7075-T6 aluminum alloy, clamp, size 39, 12 x 14mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRBA-39C-12-14>

## Technical Specifications

|                                      |                        |
|--------------------------------------|------------------------|
| <b>Brand</b>                         | Sung-II Machinery      |
| <b>Item</b>                          | Drive coupling         |
| <b>Coupling Type</b>                 | Servo-beam             |
| <b>Material</b>                      | 7075-T6 aluminum alloy |
| <b>Rated Torque</b>                  | 7 N-m                  |
| <b>Maximum Torque</b>                | 14 N-m                 |
| <b>Maximum Angular Misalignment</b>  | 2.5 degrees            |
| <b>Maximum Parallel Misalignment</b> | 0.25mm                 |

|                                     |       |
|-------------------------------------|-------|
| <b>Maximum RPM</b>                  | 10000 |
| <b>Attachment Style</b>             | Clamp |
| <b>Coupling Size</b>                | 39    |
| <b>Bore Diameter</b>                | 12mm  |
| <b>Bore Diameter 2</b>              | 14mm  |
| <b>Outside Diameter</b>             | 39mm  |
| <b>Clamp Screw Fastening Torque</b> | 8 N-m |
| <b>Clamp Screw Size</b>             | M5    |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | None  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SRBA-39C-12-14.pdf>  
See store item page for other formats.