


Q8602-1 Cut Sheet



Quabbin RS-422 low capacitance data serial cable, shielded, 1 twisted pair, 24 AWG, 7-stranded, tinned copper, foam polypropylene conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q8602-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Protocol	Serial
Wire/Cable Type	RS-422 low capacitance data and serial
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2919
Application	Data
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	1 twisted pair
Conductor Size	24 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	Foam polypropylene
Conductor Insulation Color	Black and red
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.207in
Bulk Length	Cut to length

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	E69976
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement