

# QTA-E180808CSWF Cut Sheet



Quadritalia OKK series enclosure kit, NEMA 12, 1800 x 800 x 800mm (HxWxD), freestanding, carbon steel, RAL 7035 light gray, powder coat finish, single-door, acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/QTA-E180808CSWF>

## Technical Specifications

|                                     |  |
|-------------------------------------|--|
| <b>Brand</b>                        | Quadritalia  |
| <b>Item</b>                         | Enclosure kit  |
| <b>Series</b>                       | OKK  |
| <b>NEMA Rating</b>                  | 12   |
| <b>IP Rating</b>                    | IP55   |
| <b>Nominal Enclosure Dimensions</b> | 1800 x 800 x 800mm (HxWxD)   |
| <b>Enclosure Height</b>             | 1807.00mm  |
| <b>Enclosure Width</b>              | 812.00mm   |
| <b>Enclosure Depth</b>              | 812.00mm   |
| <b>Mounting</b>                     | Freestanding   |
| <b>Dual Access</b>                  | No   |
| <b>Material</b>                     | Carbon steel   |
| <b>Color</b>                        | RAL 7035 light gray  |
| <b>Finish</b>                       | Powder coat  |
| <b>Cover Type</b>                   | Single-door  |
| <b>Window Material</b>              | Acrylic  |
| <b>Kit Includes</b>                 | (1) MTK180-4, (1) OKKTB8080, (1) PNA188, (1) DTE188, (1) RPE188 and (1) DLK188 |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E503249                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 115232                                 |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |