

STP-MTRD-17038 Cut Sheet



SureStep DC integrated stepper motor/drive, microstepping, NEMA 17 frame, IP20, 2A, 12-48 VDC, bipolar, 68 oz-in holding torque, 1.8-degree step angle, 200 to 25000 steps per revolution.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/STP-MTRD-17038>

Technical Specifications

Brand	SureStep
Item	Integrated stepper motor/drive
Voltage Type	DC
Controller Type	Microstepping
Amperage Rating	2A
Number of Output Phases	2
Voltage Rating	12-48 VDC
Winding Type Control	Bipolar
Output Type	MOSFET, dual H-bridge and 4-quadrant output
Current Control	4-state PWM at 16 kHz
Step Angle	1.8-degree
Steps per Revolution	200 to 25000
Temperature Rating	0 to 40 deg C
Enclosure Type	Enclosed
Integrated Brake	No
Motor Frame	NEMA 17
IP Rating	IP20
Shaft Type	Single
Shaft Diameter	5mm
Holding Torque Rating	68 oz-in

Control Mode	Position
Command Signal(s)	<ul style="list-style-type: none">• step and direction• CW/CCW
Number of Discrete Input Points	3
Nominal Input Voltage	5-24 VDC
Discrete Input Type	Sinking/sourcing
Number of Discrete Output Points	1
Nominal Output Voltage	5-24 VDC
Discrete Output Type	Sinking/sourcing
Tuning Mode	Pre-tuned
Idle Current Reduction	Yes
Drive Features	Self-test, anti-resonance (electronic damping), torque ripple smoothing and command signal filtering
Protection Type(s)	<ul style="list-style-type: none">• overvoltage• undervoltage• overcurrent• over-temperature
Configuration	Dipswitch
Includes	(1) 1ft control cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/STP-MTRD-17038.pdf>
See store item page for other formats.