

T23137 Cut Sheet



TITAN digital torque wrench, 1/2in drive, 30–150 lb-ft set point, ±4% (DIN ISO 6789) accuracy, digital torque value, LED, vibration, and audible tone at 70%, 80%, 90%, and 100% of set torque, 5 degrees return angle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T23137>

Technical Specifications

Brand	TITAN	Return Angle	5 degrees
Item	Torque wrench	Handle Type	Rubberized non-slip handle
Display Type	Digital	Tool Features	Reversible LCD display
Setpoint Range	30–150 lb-ft	Insulated	No
Accuracy	±4% (DIN ISO 6789)	Ratcheting	Yes
Scale	Digital torque value	Overall Length	16.5in (418mm)
Indicator	LED, vibration, and audible tone at 70%, 80%, 90%, and 100% of set torque	Application	Ratcheting and torque driving
Drive Size	1/2in	Includes	(2) AAA batteries, storage case, instruction manual, certificate of calibration
Lock Mechanism	Ballpoint socket	Additional Information	(5) torque unit options available: ft·lb, in·lb, N·m, kg·cm, kg·m
Directional Change	Switch lever		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document