

# SCE-HE04W120V Cut Sheet



Saginaw air-to-air heat exchanger, 7.2 W/deg C (4 W/deg F), 120 VAC operating voltage, 50/60 Hz, 1.10A running current, side mount, aluzinc coated steel, RAL 7035 light gray, textured powder coat finish. For use with NEMA/UL Type 3R & 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-HE04W120V>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Air-to-air Heat exchanger
<b>Cooling Capacity</b>	7.2 W/deg C (4 W/deg F)
<b>Operating Voltage</b>	120 VAC
<b>Frequency</b>	50/60 Hz
<b>Running Current</b>	1.10A
<b>Mounting</b>	Side
<b>Housing Material</b>	Aluzinc coated steel

<b>Color</b>	RAL 7035 light gray
<b>Finish</b>	Textured powder coat
<b>For Use With</b>	NEMA/UL Type 3R & 12 enclosures
<b>Includes</b>	Mounting template and hardware
<b>Dangerous Goods</b>	<ul style="list-style-type: none"><li>• Packaging Instructions: 200</li><li>• UN Number: 3159</li><li>• Hazard Type: Compressed Gas</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E498756
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SCE-HE04W120V.pdf>  
See store item page for other formats.