


# THMK-A01L10-01 Cut Sheet



ProSense temperature sensor, Type K thermocouple, armor adjustable immersion probe, grounded, 1/4in insertion length, 3/16in probe diameter, stainless steel sheath, bayonet cap process connection, 10ft 20 AWG wire leads.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMK-A01L10-01>

## Technical Specifications

|                  |                                  |
|------------------|----------------------------------|
| Brand            | ProSense                         |
| Item             | Temperature sensor               |
| Sensor Element   | Type K thermocouple              |
| Sensor Type      | Armor adjustable immersion probe |
| Accuracy         | Standard limits of error         |
| Junction Type    | Grounded                         |
| Insertion Length | 1/4in                            |
| Probe Diameter   | 3/16in                           |

|                               |  |
|-------------------------------|--|
| Sheath Material               | Stainless steel                          |
| Process Connection            | Bayonet cap                              |
| Bayonet Cap                   | 7/16in inside diameter single slot       |
| Electrical Connection         | 10ft 20 AWG wire leads                   |
| Conductor Insulation Material | Fiberglass and stainless steel overbraid |
| Temperature Sensing Range     | 32 to 900 deg F                          |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/THMK-A01L10-01.pdf>  
See store item page for other formats.