

THMWJ-20-8SS-P-1 Cut Sheet

TE Wire & Cable Type J thermocouple PLTC and ITC extension cable, individual and overall shielded, 8 twisted pairs, 20 AWG, iron and copper-nickel, PVC conductor insulation material, white and red, PVC jacket, black, cut to length.



For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWJ-20-8SS-P-1>

Technical Specifications

Brand	TE Wire & Cable
Item	Cable
Sensor Type	Type J thermocouple
Wire/Cable Type	Extension
UL Wire/Cable Type	PLTC and ITC
Application	Temperature
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	8 twisted pairs
Conductor Size	20 AWG
Conductor Stranding	Solid
Conductor Material	Iron and copper-nickel
Conductor Insulation Material	PVC
Conductor Insulation Color	White and red

Shielding	Individual and overall shielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.579in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 110ft = 14 x 7in Reel, 111 to 157ft = 14 x 10in Reel, 158 to 244ft = 16 x 10in Reel, 245 to 343ft = 18 x 10in Reel, 344 to 446ft = 18 x 13in Reel, 447 to 959ft = 24 x 17in Wooden Reel, 960 to 1578ft = 30 x 17in Wooden Reel, 1579 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E54438
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	RoHS Statement