

# SCU-1600 Cut Sheet



ProSense signal conditioner, isolated, current, voltage, RTD, thermocouple or potentiometer input, deg F or deg C, current, voltage or relay output, 21.6-253 VAC/19.2-300 VDC operating voltage, 35mm DIN rail mount, removable screw terminal plugs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCU-1600>

## Technical Specifications

Brand	ProSense
Item	Signal conditioner
Isolation	Isolated
Field Configurable	Yes
Input Current Signal Range	0-20 mA, 4-20 mA
Input Potentiometer Resistance	10-100k Ohms
Input RTD Signal Types	Pt10, Pt20, Pt50, Pt100, Pt200, Pt250, Pt300, Pt400, Pt500, Pt1000, Ni50, Ni100, Ni120, Ni1000, Cu10, Cu20, Cu50 and Cu100
Input Thermocouple Signal Type	J, K, N, T, E, R, S, B, L, U, W3, W5, LR
Input Voltage Signal Range	0-1 VDC, 0.2-1 VDC, 0-5 VDC, 1-5 VDC, 0-10 VDC, 2-10 VDC, 0-12 VDC
Programmable Temperature Range	Deg F or deg C
Output Current Signal Range	0-20 mA, 4-20 mA, 20-0 mA and 20-4 mA
Output Voltage Signal Range	0-1 VDC, 0.2-1 VDC, 0-5 VDC, 1-5 VDC, 0-10 VDC, 2-10 VDC, 1-0 VDC, 1-0.2 VDC, 5-0 VDC, 5-1 VDC, 10-0 VDC and 10-2 VDC
Relay Configuration	(2) Form A (SPST) relays
Load Current	230 VAC 2A/24 VDC 1A maximum
Operating Voltage	21.6-253 VAC/19.2-300 VDC
Housing Material	Plastic
Mounting	35mm DIN rail
Electrical Connection	Removable screw terminal plugs
Requires	SCU-PDM2 for programming, sold separately

## Agency Approvals

UL Listed File #	E191072
CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">FM Approval Document</a>