


THMWK-20-4S-P-1 Cut Sheet

TE Wire & Cable Type K thermocouple PLTC and ITC extension cable, shielded, 4 twisted pairs, 20 AWG, nickel-chromium and nickel-aluminum, PVC conductor insulation material, yellow and red, PVC jacket, yellow, cut to length.



For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWK-20-4S-P-1>

Technical Specifications

Brand	TE Wire & Cable
Item	Cable
Sensor Type	Type K thermocouple
Wire/Cable Type	Extension
UL Wire/Cable Type	PLTC and ITC
Application	Temperature
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	4 twisted pairs
Conductor Size	20 AWG
Conductor Stranding	Solid
Conductor Material	Nickel-chromium and nickel-aluminum
Conductor Insulation Material	PVC
Conductor Insulation Color	Yellow and red

Shielding	Shielded
Jacket Material	PVC
Jacket Color	Yellow
Nominal Overall Cable Diameter	0.377in
Bulk Length	Cut to length
Package Type	1 to 75ft = Coil, 76 to 260ft = 14 x 7in Reel, 261 to 372ft = 14 x 10in Reel, 373 to 575ft = 16 x 10in Reel, 576 to 810ft = 18 x 10in Reel, 811 to 1054ft = 18 x 13in Reel, 1055 to 2264ft = 24 x 17in Wooden Reel, 2265 to 3722ft = 30 x 17in Wooden Reel, 3723 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E54438
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	RoHS Statement