

SE-SW5M-2ST Cut Sheet



STRIDE industrial managed Ethernet switch, 5 ports, (3) Ethernet 10/100Base-T (RJ45) and (2) multi-mode ST 100FX fiber port(s), Modbus TCP, -40 to +75 deg C, metal housing, IP40, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-SW5M-2ST>

Technical Specifications

| | |
|---|--|
| Brand | STRIDE |
| Item | Ethernet switch |
| Grade | Industrial |
| Switch Type | Managed |
| Number of Ports | 5 |
| Communication Port and Connection Type(s) | <ul style="list-style-type: none">• (3) Ethernet 10/100Base-T (RJ45)• (2) multi-mode ST 100FX fiber |
| Port Protocol(s) | <ul style="list-style-type: none">• Modbus TCP• webserver (secure HTTPs) |

| | |
|-----------------------|--|
| Port Speed(s) | <ul style="list-style-type: none">• 10/100 Mbps auto-detect• 100 Mbps fiber |
| Operating Temperature | -40 to +75 deg C |
| Housing Material | Metal |
| IP Rating | IP40 |
| Mounting | 35mm DIN rail |
| Application | Hazardous location rated |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E200031 |
| UL Recognized File # | None |
| UL Hazardous File # | E200031 |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SE-SW5M-2ST.pdf>
See store item page for other formats.