

SE-SW5U-ST Cut Sheet



STRIDE industrial unmanaged Ethernet switch, 5 ports, (4) Ethernet 10/100Base-T (RJ45) and (1) multi-mode ST 100FX fiber port(s), -10 to +60 deg C, plastic housing, IP40, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-SW5U-ST>

Technical Specifications

Brand	STRIDE
Item	Ethernet switch
Grade	Industrial
Switch Type	Unmanaged
Number of Ports	5
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (4) Ethernet 10/100Base-T (RJ45)• (1) multi-mode ST 100FX fiber
Port Speed(s)	<ul style="list-style-type: none">• 10/100 Mbps auto-detect• 100 Mbps fiber
Operating Temperature	-10 to +60 deg C
Housing Material	Plastic
IP Rating	IP40
Mounting	35mm DIN rail
Application	Hazardous location rated

Agency Approvals

UL Listed File #	E200031
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document