

# SE-SW9U-ST Cut Sheet



STRIDE industrial unmanaged Ethernet switch, 9 ports, (8) Ethernet 10/100Base-T (RJ45) and (1) multi-mode ST 100FX fiber port(s), -10 to +60 deg C, plastic housing, IP40, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-SW9U-ST>

## Technical Specifications

Brand	STRIDE
Item	Ethernet switch
Grade	Industrial
Switch Type	Unmanaged
Number of Ports	9
Communication Port and Connection Type(s)	<ul style="list-style-type: none"><li>• (8) Ethernet 10/100Base-T (RJ45)</li><li>• (1) multi-mode ST 100FX fiber</li></ul>
Port Speed(s)	<ul style="list-style-type: none"><li>• 10/100 Mbps auto-detect</li><li>• 100 Mbps fiber</li></ul>
Operating Temperature	-10 to +60 deg C
Housing Material	Plastic
IP Rating	IP40
Mounting	35mm DIN rail
Application	Hazardous location rated

## Agency Approvals

UL Listed File #	E200031
UL Recognized File #	None
UL Hazardous File #	E200031
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SE-SW9U-ST.pdf>  
See store item page for other formats.