

SE2-SW16M Cut Sheet



STRIDE industrial managed Ethernet switch, 16 ports, (16) Ethernet 10/100Base-T (RJ45) port(s), EtherNet/IP and Modbus TCP, -40 to +75 deg C, metal housing, IP40, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE2-SW16M>

Technical Specifications

Brand	STRIDE
Item	Ethernet switch
Grade	Industrial
Switch Type	Managed
Number of Ports	16
Communication Port and Connection Type(s)	(16) Ethernet 10/100Base-T (RJ45)
Port Protocol(s)	<ul style="list-style-type: none">• EtherNet/IP• Modbus TCP• webserver (secure HTTPs)

Port Speed(s)	10/100 Mbps auto-detect
Operating Temperature	-40 to +75 deg C
Housing Material	Metal
IP Rating	IP40
Mounting	35mm DIN rail
Application	Hazardous location rated

Agency Approvals

UL Listed File #	E200031
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SE2-SW16M.pdf>
See store item page for other formats.