

SE3-SWP2A5U-T Cut Sheet



STRIDE industrial unmanaged PoE+ switch, IEEE 802.3af/at, 120W, 5 ports, (4) PoE+ 10/100Base-T (RJ45) and (1) Ethernet 10/100Base-T (RJ45) port(s), 12-36 VDC nominal input, -40 to +75 deg C, NEMA TS2, 35mm DIN rail or panel mount, hazardous location rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE3-SWP2A5U-T>

Technical Specifications

| | |
|--|---|
| Brand | STRIDE |
| Item | PoE+ switch |
| Grade | Industrial |
| Switch Type | Unmanaged |
| PoE Standard | IEEE 802.3af/at |
| Maximum PoE Output Power | 120W |
| Maximum PoE Output Power per Port | 30W |
| Number of Ports | 5 |
| Communication Port and Connection Type(s) | <ul style="list-style-type: none">• (4) PoE+ 10/100Base-T (RJ45)• (1) Ethernet 10/100Base-T (RJ45) |
| Port Speed(s) | 10/100 Mbps auto-detect |
| Nominal Input Voltage | 12-36 VDC |
| Number of Output Points | 1 |

| | |
|------------------------------------|---|
| Nominal Output Voltage | 24 VDC |
| Relay Configuration | (1) Form A (SPST) relay |
| Number of Isolated Commons | 1 |
| Number of Points per Common | 1 |
| Load Current | 1A/point |
| Operating Temperature | -40 to +75 deg C |
| Housing Material | Metal |
| IP Rating | IP30 |
| NEMA Rating | TS2 |
| Mounting | 35mm DIN rail or panel |
| Additional Information | Capable of being powered by 12-36 VDC while still providing 48-52 VDC required by the PoE standard. |
| Application | Hazardous location rated |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E157382 |
| UL Recognized File # | None |
| UL Hazardous File # | ANSI/ISA 12.12.01 |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SE3-SWP2A5U-T.pdf>
See store item page for other formats.