

SE3-SWP2A7U-2P-T Cut Sheet



STRIDE industrial unmanaged PoE+ switch, IEEE 802.3af/at, up to 120W, 7 ports, (4) PoE+ 10/100Base-T (RJ45), (1) Ethernet 10/100Base-T (RJ45) and (2) SFP combo Gigabit port(s), 12-55 VDC nominal input, -40 to +75 deg C, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE3-SWP2A7U-2P-T>

Technical Specifications

Brand	STRIDE
Item	PoE+ switch
Grade	Industrial
Switch Type	Unmanaged
PoE Standard	IEEE 802.3af/at
Maximum PoE Output Power	60W @ 12-36 VDC, 120W @ 37-55 VDC
Maximum PoE Output Power per Port	30W
Number of Ports	7
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (4) PoE+ 10/100Base-T (RJ45)• (1) Ethernet 10/100Base-T (RJ45)• (2) SFP combo Gigabit
Port Speed(s)	<ul style="list-style-type: none">• 10/100 Mbps auto-detect• 100/1000 Mbps fiber
Nominal Input Voltage	12-55 VDC
Number of Output Points	1

Nominal Output Voltage	24 VDC
Relay Configuration	(1) Form A (SPST) relay
Number of Isolated Commons	1
Number of Points per Common	1
Load Current	1A/point
Operating Temperature	-40 to +75 deg C
Housing Material	Metal
IP Rating	IP30
Mounting	35mm DIN rail or panel
Additional Information	Capable of being powered by 12-52 VDC while still providing 48-52 VDC required by the PoE standard. Optional SFP modules sold separately.
Application	Hazardous location rated

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	ANSI/ISA 12.12.01
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SE3-SWP2A7U-2P-T.pdf>
See store item page for other formats.