

SE3-SWP2B5UG-1P-T Cut Sheet



STRIDE industrial unmanaged PoE++ switch, IEEE 802.3af/at/bt, up to 240W, 5 ports, (4) PoE++ 10/100/1000Base-T (RJ45) and (1) SFP combo Gigabit port(s), 9-55 VDC nominal input, -40 to +75 deg C, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE3-SWP2B5UG-1P-T>

Technical Specifications

Brand	STRIDE
Item	PoE++ switch
Grade	Industrial
Switch Type	Unmanaged
PoE Standard	IEEE 802.3af/at/bt
Maximum PoE Output Power	60W @ 9 VDC, 90W @ 12 VDC, 150W @ 24 VDC, 240W @ 48-55 VDC (with iPoE budget control)
Maximum PoE Output Power per Port	90W
Number of Ports	5
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (4) PoE++ 10/100/1000Base-T (RJ45)• (1) SFP combo Gigabit
Port Speed(s)	<ul style="list-style-type: none">• 10/100/1000 Mbps auto-detect• 100/1000 Mbps fiber
Nominal Input Voltage	9-55 VDC

Number of Output Points	1
Nominal Output Voltage	24 VDC
Relay Configuration	(1) Form A (SPST) relay
Number of Isolated Commons	1
Number of Points per Common	1
Load Current	1A/point
Operating Temperature	-40 to +75 deg C
Housing Material	Metal
IP Rating	IP30
Mounting	35mm DIN rail or panel
Additional Information	Redundant power input design, 9-55 VDC. Optional SFP modules sold separately

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SE3-SWP2B5UG-1P-T.pdf>
See store item page for other formats.