

SEP1-SWP2A8U-T Cut Sheet



STRIDE PRO industrial unmanaged+ PoE+ switch, IEEE 802.3af/at, 200W, 8 ports, (8) PoE+ 10/100Base-T (RJ45) port(s), 12–36 VDC nominal input, -40 to +75 °C, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEP1-SWP2A8U-T>

Technical Specifications

Brand	STRIDE PRO	Port Speed(s)	10/100 Mbps auto-detect
Item	PoE+ switch	Redundant Input Power	Yes
Grade	Industrial	Nominal Input Voltage	12–36 VDC
Switch Type	Unmanaged+	Number of Output Points	1
PoE Standard	IEEE 802.3af/at	Nominal Output Voltage	24 VDC
Maximum PoE Output Power	200W	Relay Configuration	(1) Form A (SPST) relay
Maximum PoE Output Power per Port	30W	Number of Isolated Commons	1
Number of Ports	8	Number of Points per Common	1
Communication Port and Connection Type(s)	(8) PoE+ 10/100Base-T (RJ45)	Load Current	1A/point
Communication Standard(s)	• IEEE 802.3 10Base-T • IEEE 802.3u 100Base-TX/FX • IEEE 802.3x Flow Control • IEEE 802.3af PoE • IEEE 802.at PoE+ • IEEE 802.1D Broadcast Storm Protection (BSP)	Operating Temperature	-40 to +75 °C
		Housing Material	Metal
		IP Rating	IP30
		Mounting	35mm DIN rail or panel
		Additional Information	Port Prioritization

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SEP1-SWP2A8U-T.pdf>
See store item page for other formats.