

# SFC-38-8-12 Cut Sheet



Sung-II Machinery drive coupling, double loop, nickel plated steel, setscrew, size 38, 8 x 12mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SFC-38-8-12>

## Technical Specifications

<b>Brand</b>	Sung-II Machinery
<b>Item</b>	Drive coupling
<b>Coupling Type</b>	Double loop
<b>Material</b>	Nickel plated steel
<b>Maximum Torque</b>	1.4 N·m
<b>Maximum Angular Misalignment</b>	10 degrees
<b>Maximum Parallel Misalignment</b>	2.5mm
<b>Maximum RPM</b>	3000

<b>Attachment Style</b>	Setscrew
<b>Coupling Size</b>	38
<b>Overall Length</b>	35mm
<b>Bore Diameter</b>	8mm
<b>Bore Diameter 2</b>	12mm
<b>Outside Diameter</b>	32mm
<b>Clamp Screw Fastening Torque</b>	1.7 N·m
<b>Clamp Screw Size</b>	M4-0.7 x 6mm

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SFC-38-8-12.pdf>  
See store item page for other formats.