

SFC516KC1 Cut Sheet



Minerallac hammer-on flange clamp conduit hanger assembly, spring clip, back mount, 25 lbs, UL Type UL 2239. Package of 100. For use with 5/16 to 1/2in flanges and 1in conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SFC516KC1>

Technical Specifications

Brand	Minerallac	Electrical Metallic Tubing (EMT) Trade Size	1in
Item	Conduit hanger assembly	Intermediate Metallic Conduit (IMC) Trade Size	1in
Mount Type	Hammer-on flange clamp	Reduced Wall Flexible Metal Conduit Trade Size	3/4in
Hanger Type	Spring clip	Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1in
Mount Side	Back	UL Type	UL 2239
Material	Spring steel	Quantity per Pack	100
Finish	Zinc phosphate plated	For Use With	5/16 to 1/2in flanges and 1in conduit
Minimum Flange Thickness	5/16in		
Maximum Flange Thickness	1/2in		
Load Rating	25 lbs		
Outside Diameter	1.11in-1.31in		
Rigid Metallic Conduit (RMC) Trade Size	1in		

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document