

# SHDS-88C-34.92-34.92 Cut Sheet



Sung-II Machinery drive coupling, high torque disc, 7075-T6 aluminum alloy, clamp, size 88, 1-3/8 x 1-3/8in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHDS-88C-34.92-34.92>

## Technical Specifications

<b>Brand</b>	Sung-II Machinery
<b>Item</b>	Drive coupling
<b>Coupling Type</b>	High torque disc
<b>Material</b>	7075-T6 aluminum alloy
<b>Rated Torque</b>	180 N·m
<b>Maximum Torque</b>	360 N·m
<b>Maximum Angular Misalignment</b>	0.7 degrees
<b>Maximum Parallel Misalignment</b>	0.02mm
<b>Maximum RPM</b>	5500

<b>Attachment Style</b>	Clamp
<b>Coupling Size</b>	88
<b>Overall Length</b>	69.9mm
<b>Bore Diameter</b>	1-3/8in
<b>Bore Diameter 2</b>	1-3/8in
<b>Outside Diameter</b>	88mm
<b>Clamp Screw Fastening Torque</b>	30 N·m
<b>Clamp Screw Size</b>	M8-1.25 x 25mm

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SHDS-88C-34.92-34.92.pdf>  
See store item page for other formats.