

# SHR-38C-16-19 Cut Sheet



Sung-II Machinery drive coupling, servo high gain, aluminum alloy, clamp, size 38, 16 x 19mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHR-38C-16-19>

## Technical Specifications

<b>Brand</b>	Sung-II Machinery
<b>Item</b>	Drive coupling
<b>Coupling Type</b>	Servo high gain
<b>Material</b>	Aluminum alloy
<b>Rated Torque</b>	12 N·m
<b>Maximum Torque</b>	24 N·m
<b>Maximum Angular Misalignment</b>	1.5 degrees
<b>Maximum Parallel Misalignment</b>	0.2mm
<b>Maximum RPM</b>	16000

<b>Attachment Style</b>	Clamp
<b>Coupling Size</b>	38
<b>Overall Length</b>	47mm
<b>Bore Diameter</b>	16mm
<b>Bore Diameter 2</b>	19mm
<b>Outside Diameter</b>	37.8mm
<b>Clamp Screw Fastening Torque</b>	3.7 N·m
<b>Clamp Screw Size</b>	M4-0.7 x 14mm

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SHR-38C-16-19.pdf>  
See store item page for other formats.