

SHR-38C-19-19 Cut Sheet



Sung-II Machinery drive coupling, servo high gain, aluminum alloy, clamp, size 38, 19 x 19mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHR-38C-19-19>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo high gain
Material	Aluminum alloy
Rated Torque	12 N-m
Maximum Torque	24 N-m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	0.2mm

Maximum RPM	16000
Attachment Style	Clamp
Coupling Size	38
Bore Diameter	19mm
Bore Diameter 2	19mm
Outside Diameter	37.8mm
Clamp Screw Fastening Torque	3.7 N-m
Clamp Screw Size	M4

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SHR-38C-19-19.pdf>
See store item page for other formats.