

SHR-43C-14-22 Cut Sheet



Sung-II Machinery drive coupling, servo high gain, aluminum alloy, clamp, size 43, 14 x 22mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHR-43C-14-22>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo high gain
Material	Aluminum alloy
Rated Torque	16 N·m
Maximum Torque	32 N·m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	0.2mm
Maximum RPM	14000

Attachment Style	Clamp
Coupling Size	43
Overall Length	48mm
Bore Diameter	14mm
Bore Diameter 2	22mm
Outside Diameter	42.8mm
Clamp Screw Fastening Torque	3.7 N·m
Clamp Screw Size	M4-0.7 x 14mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SHR-43C-14-22.pdf>
See store item page for other formats.