

SHR-55C-22.225-25 Cut Sheet



Sung-II Machinery drive coupling, servo high gain, aluminum alloy, clamp, size 55, 7/8in x 25mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHR-55C-22.225-25>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo high gain
Material	Aluminum alloy
Rated Torque	32 N·m
Maximum Torque	64 N·m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	0.2mm
Maximum RPM	11000

Attachment Style	Clamp
Coupling Size	55
Overall Length	59mm
Bore Diameter	7/8in
Bore Diameter 2	25mm
Outside Diameter	54.8mm
Clamp Screw Fastening Torque	8.5 N·m
Clamp Screw Size	M5-0.8 x 20mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SHR-55C-22.225-25.pdf>
See store item page for other formats.