

SHR-68C-32-32 Cut Sheet



Sung-II Machinery drive coupling, servo high gain, aluminum alloy, clamp, size 68, 32 x 32mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHR-68C-32-32>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo high gain
Material	Aluminum alloy
Rated Torque	65 N·m
Maximum Torque	130 N·m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	0.2mm
Maximum RPM	9000

Attachment Style	Clamp
Coupling Size	68
Overall Length	75mm
Bore Diameter	32mm
Bore Diameter 2	32mm
Outside Diameter	67.8mm
Clamp Screw Fastening Torque	13 N·m
Clamp Screw Size	M6-1.0 x 25mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SHR-68C-32-32.pdf>
See store item page for other formats.