

TMT36-13C0/101 Cut Sheet



Endress+Hauser iTEMP programmable temperature transmitter, non-isolated, Input: 1-channel, RTD, deg F or deg C, Output: 1-channel, IO-Link, 18-30 VDC operating voltage, DIN Form B connection head mount, push-in terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TMT36-13C0/101>

Technical Specifications

Brand	Endress+Hauser
Item	Programmable temperature transmitter
Series	iTEMP
Isolation	Non-isolated
Field Configurable	Yes
Number Of Input Channels	1
Input	RTD
Input RTD Signal Types	Pt100 and Pt1000
Programmable Temperature Range	Deg F or deg C
Number Of Output Channels	1
Output	IO-Link

Communication Port and Connection Type(s)	(1) 4-pin M12 A-coded (IO-Link)
Port Protocol(s)	IO-Link Class A Device
Port Speed(s)	IO-Link COM2
IO-Link Version	IO-Link v1.1.3
Standard I/O Mode Supported	No
Operating Voltage	18-30 VDC
Housing Material	Polycarbonate
Mounting	DIN Form B connection head
Electrical Connection	Push-in terminals
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	200600
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document