

# TP19U115B1 Cut Sheet



Fandis Virdis series exhaust fan, top mount, 338 CFM, 115 VAC operating voltage, NEMA 12, indoor use only, 6.89 x 6.89in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TP19U115B1>

## Technical Specifications

<b>Brand</b>	Fandis	<b>Electrical Connection</b>	Terminal block
<b>Series</b>	Virdis series	<b>Maximum Static Pressure</b>	565Pa
<b>Airflow Direction</b>	Exhaust	<b>Operating Temperature</b>	14 to 131 deg F
<b>Item</b>	Fan	<b>Average Noise Level</b>	73 dbA
<b>Mounting</b>	Top	<b>NEMA Rating</b>	12
<b>With Air Flaps</b>	No	<b>Application</b>	Indoor use only
<b>Free Airflow</b>	338 CFM	<b>IP Rating</b>	IP24
<b>Airflow with Grill and Filter(s)</b>	297 CFM	<b>Enclosure Cutout</b>	6.89 x 6.89in
<b>Operating Voltage</b>	115 VAC	<b>Color</b>	RAL 7035 light gray
<b>Frequency</b>	60 Hz	<b>Includes</b>	Mounting screws
<b>Power Consumption</b>	97W	<b>Additional Information</b>	Purchase intake grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Refer to technical specifications for 50Hz performance data
<b>Current Draw</b>	850 mA		

## Agency Approvals

<b>UL Listed File #</b>	E500932
<b>UL Recognized File #</b>	E237844
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	260922
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>