


SJEOOW-10-4BK-1 Cut Sheet



Southwire portable cord, unshielded, SJEOOW, 300V, 4 conductors (includes ground), 10 AWG, TPE conductor insulation material, black, white, red and green, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SJEOOW-10-4BK-1>

Technical Specifications

Brand	Southwire
Item	Cord
Wire/Cable Type	Portable
UL Wire/Cable Type	SJEOOW
Applicable Standards	UL 62
Application	General purpose
Flexibility	Flexible
Voltage Rating	300V
Conductors	4 conductors (includes ground)
Conductor Size	10 AWG
Conductor Stranding	104-stranded
Conductor Material	Bare copper
Conductor Insulation Material	TPE
Conductor Insulation Color	Black, white, red and green

Shielding	Unshielded
Jacket Material	TPE
Jacket Color	Black
Nominal Overall Cable Diameter	0.64in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 90ft = 14 x 7in Reel, 91 to 130ft = 14 x 10in Reel, 131 to 210ft = 16 x 10in Reel, 211 to 290ft = 18 x 10in Reel, 291 to 380ft = 18 x 13in Reel, 381 to 830ft = 24 x 17in Wooden Reel, 831 to 1360ft = 30 x 17in Wooden Reel, 1361 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E46194
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement