

TRU-C23PA-TMS-603 Cut Sheet



Contrinex photoelectric sensor, rectangular, polarized retroreflective, ultra violet light emission, 1m sensing distance, complementary light-on/dark-on, PNP, teach-in button, 4-wire, 4-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TRU-C23PA-TMS-603>

Technical Specifications

Brand	Contrinex
Item	Photoelectric sensor
Shape	Rectangular
Housing Size	20 x 10 x 30mm
IP Rating	IP67
Housing Material	ABS plastic
Sensing Method	Polarized retroreflective
Sensing Technology	Clear object detection
Operating Voltage	10-30 VDC
Number of Wires	4
Switching Output	PNP
Sensing Distance	1m
Sensitivity	Teach-in button
Operation Mode	Complementary light-on/dark-on

Switching Frequency	1 kHz
Light emission	Ultra violet
IO-Link Compatible	Yes
Connection	4-pin M8 quick-disconnect
Communication Port and Connection Type(s)	(1) 4-pin M8 (IO-Link) port(s)
Port Protocol(s)	IO-Link Class A Device
Port Speed(s)	IO-Link COM2
IO-Link Version	IO-Link v1.0
Standard I/O Mode Supported	Yes
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E239373
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document