

# SMR5-09 Cut Sheet



IronHorse heavy duty shaft mounted gearbox, 9:1 ratio, 1-15/16in shaft input, tapered bore, maximum motor 40 hp, 2-15/16in maximum output shaft diameter, size 5 frame, cast iron housing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SMR5-09>

## Technical Specifications

<b>Brand</b>	IronHorse
<b>Item</b>	Gearbox
<b>Application</b>	General purpose
<b>Duty Rating</b>	Heavy duty
<b>Gearbox Type</b>	Shaft mounted
<b>Gear Ratio</b>	9:1
<b>Speed Rating</b>	1750 rpm input / 192 rpm output
<b>Input Configuration</b>	1-15/16in shaft
<b>Output Configuration</b>	Tapered bore

<b>Maximum Motor Size</b>	40 hp
<b>Maximum Output Shaft Diameter</b>	2-15/16in
<b>Frame</b>	Size 5
<b>Housing Material</b>	Cast iron
<b>Finish</b>	Anti-corrosion primer and paint
<b>Lubrication Type</b>	Shipped without oil - fill before use
<b>Oil Seal Type</b>	Double-lip
<b>Includes</b>	Torque arm

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SMR5-09.pdf>  
See store item page for other formats.