

# TY523M Cut Sheet



ABB - Thomas & Betts Ty-Rap series steel tooth cable tie, general purpose, nylon 6.6, 3.6in length, 0.09in width, 18 lb tensile strength, 0.6in maximum bundle diameter, natural. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TY523M>

## Technical Specifications

|                                |                      |
|--------------------------------|----------------------|
| <b>Brand</b>                   | ABB - Thomas & Betts |
| <b>Item</b>                    | Cable tie            |
| <b>Cable Tie Type</b>          | Steel tooth          |
| <b>Performance</b>             | General purpose      |
| <b>Material</b>                | Nylon 6.6            |
| <b>Series</b>                  | Ty-Rap               |
| <b>Length</b>                  | 3.6in                |
| <b>Width</b>                   | 0.09in               |
| <b>Tensile Strength</b>        | 18 lb                |
| <b>Maximum Bundle Diameter</b> | 0.6in                |

|                                 |   |
|---------------------------------|---|
| <b>Color</b>                    | Natural   |
| <b>UV Resistant</b>             | No  |
| <b>Temperature Rating</b>       | -76 to +185 °F  |
| <b>Installation Temperature</b> | -4 °F   |
| <b>Flammability</b>             | UL 94 V-2   |
| <b>UL Rating</b>                | UL 62275  |
| <b>Applicable Standards</b>     | UL 62275 (cULus), CSA C22.2 No. 62275, IEC 62275 and CE 62275 |
| <b>Quantity per Pack</b>        | 100   |

## Agency Approvals

|                         |   |
|-------------------------|---|
| <b>UL Listed File #</b> | E49405  |
| <b>CE</b>               | None  |
| <b>CSA File #</b>       | 2884  |
| <b>RoHS Status</b>      | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>         | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>            | <a href="#">RoHS Statement</a>                                      |