

SOH-43C-15.875 Cut Sheet



Sung-II Machinery drive coupling hub, Oldham, aluminum alloy, clamp, size 43, 5/8in bore. Requires SOH-43-DISC torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOH-43C-15.875>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Oldham
Material	Aluminum alloy
Rated Torque	12.5 N·m
Maximum Torque	25 N·m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	3mm
Maximum RPM	8000

Attachment Style	Clamp
Coupling Size	43
Overall Length	52mm
Bore Diameter	5/8in
Outside Diameter	43mm
Clamp Screw Fastening Torque	8 N·m
Clamp Screw Size	M5-0.8 x 16mm
Requires	SOH-43-DISC torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SOH-43C-15.875.pdf>
See store item page for other formats.