

SOH-57C-15.875 Cut Sheet



Sung-II Machinery drive coupling hub, Oldham, aluminum alloy, clamp, size 57, 5/8in bore. Requires SOH-57-DISC torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SOH-57C-15.875>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling hub
Coupling Type	Oldham
Material	Aluminum alloy
Rated Torque	34 N·m
Maximum Torque	68 N·m
Slip Torque	50 N·m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	3.5mm

Maximum RPM	6000
Attachment Style	Clamp
Coupling Size	57
Overall Length	76.2mm
Bore Diameter	5/8in
Outside Diameter	57mm
Clamp Screw Fastening Torque	13 N·m
Clamp Screw Size	M6-1.0 x 20mm
Requires	SOH-57-DISC torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SOH-57C-15.875.pdf>
See store item page for other formats.